

Phottix System

How it fits

Triggering Chart



	INDRA360 TTL	INDRA500 TTL	Mitros™+	Odin™ II	Odin™	Strato™ TTL	Strato™ II Multi	Atlas™ II	Ares™	Ares II	Juno
Phottix Odin™ II											
Triggers	✓	✓	✓	✓	✓*		✓(M)*	✓(M)*		✓(M)*	✓(M)
Triggered by			✓*	✓	✓*						
Phottix INDRA360 TTL											
Triggers											
Triggered by			✓*	✓	✓*	✓(M)	✓(M)	Sync Cord with RX	Sync Cord with RX	✓(M)*	✓(M)
Phottix INDRA500 TTL											
Triggers											
Triggered by			✓*	✓	✓*	✓(M)	✓(M)	Sync Cord with RX	Sync Cord with RX	✓(M)*	✓(M)
Phottix Mitros™+											
Triggers	✓*	✓*	✓*	✓*	✓		✓(M)	✓(M)		✓(M)*	✓(M)
Triggered by			✓	✓	✓	✓(M)	✓(M)*	Hot Shoe with RX	Hot Shoe with RX	✓(M)*	✓(M)
Phottix Odin™											
Triggers	✓*	✓*	✓*	✓*	✓		✓(M)	✓(M)		✓(M)*	✓(M)
Triggered by			✓	✓	✓						
Phottix Strato™ TTL											
Triggers	✓(M)*	✓(M)*	✓(M)*			✓	✓*				
Triggered by						✓					
Phottix Strato™ II Multi											
Triggers	✓(M)*	✓(M)*	✓(M)*				✓	✓		✓(M)*	✓(M)
Triggered by			✓*	✓(M)*	✓(M)	✓(M)	✓(M)			✓(M)*	✓(M)
Phottix Atlas™ II											
Triggers	✓(Sync Port)	✓(Sync Port)	✓(Sync Port)					✓			
Triggered by			✓(M)	✓(M)*	✓(M)*	✓(M)*	✓(M)	✓		✓(M)*	
Phottix Ares™											
Triggers	✓(Sync Port)	✓(Sync Port)	✓(Sync Port)						✓		
Triggered by									✓		
Phottix Ares II											
Triggers	✓(M)*	✓(M)*	✓(M)*				✓(M)*	✓(M)*		✓	✓(M)
Triggered by			✓(M)*	✓(M)*	✓(M)*	✓(M)*	✓(M)*			✓	✓(M)
Phottix Juno											
Triggers	✓(M)	✓(M)	✓(M)				✓(M)*	✓(M)*		✓(M)	✓
Triggered by			✓(M)	✓(M)*	✓(M)*	✓(M)*	✓(M)*			✓(M)	✓












Note: All specs are pre-production and subject to change.

- In Normal and Transmit modes only.
- * (Ch1-4)

Phottix System

How it fits

Comparison Chart

											
	INDRA360 TTL	INDRA500 TTL	Mitros™ +	Odin™ II	Odin™	Strato™ TTL	Strato™ II Multi	Atlas™ II	Ares™	Ares II	Juno
Range	100m	100m	100m+	100m	100m+	100m+	150m+	350m	200m+	150m	200m
TTL	✓	✓	✓	✓	✓	✓					
Channels	32	32	32	32	4	4	4	4	8	16	16
Groups	5	5	5	5	3		4			4	4
Max. Sync Speed	1/8000s	1/8000s	1/8000s	1/8000s	1/8000s	1/8000s	1/250s	1/250s	1/250s	1/250s	1/250s
Overdrive Sync (ODS)				✓	✓						
High Speed Sync	✓	✓	✓	✓	✓	✓					
Second Curtain Sync	✓	✓	✓	✓	✓	✓					
Pass-through hot shoe							✓				
LCD Screen	✓	✓	✓	✓	✓	✓				✓	✓
Canon Version	✓+	✓+	✓	✓	✓	✓	✓				
Nikon Version	✓+	✓+	✓	✓	✓	✓	✓				
Sony Version	✓+	✓+	✓	✓	✓		✓				
Batteries	5000 mAh Li-Ion	4000 mAh Li-Ion	AA	AA	AA	AA	AAA	AA	AA	AA	AA
Wired Remote						✓	✓	✓			
Wireless Remote						✓	✓	✓			
Transmitter Sync Port							✓				

* See compatibility chart for full details.

NOTE for Mitros™+: RX Only-TX 4 Channels 3 Groups

✓+ - INDRA360 / 500 Has Canon, Nikon and Sony TTL Built IN.

Channels 1-4 compatible with Phottix Strato II. Digital ID Channels 5-16.